

350 overhead suspended shield & LED 130F lamp

350/45/LED130F-0031 (250 cm ceiling track, 40 cm x 50 cm lead glass shield & LED 130F examination lamp)

Track mounted, moveable upper body protection

This 40 cm x 50 cm shield uses 2.2 mm equivalent lead glass (@150 kV) for effective protection of the eyes and thyroid. The robust yoke assembly provides stability and protection to the window. The shield is fitted with a 0.5 mm Pb equivalent flexible curtain which is suspended beneath to further reduce scatter radiation. The LED 130F lamp is a compact yet practical examination light with a light output of 70,000 lux.

350 x-ray shield, 40 cm x 50 cm

- > Protection for the eyes and thyroid.
- > Landscape, 40 cm x 50 cm transparent shield with 2.2 mm equivalent lead glass (@150 kV).
- Suspended, 0.5 mm Pb equivalent flexible curtain. 20 cm in depth.
- > Pivots on the central horizontal axis.

LED 130F examination lamp

- Light intensity at 1 metre: 70,000 Lux.
- Colour rendering index R_a 96.
- Focusable light field size: 13 cm to 19 cm.
- Electronic light intensity control at lamp head: 50% to 100%.
- > Colour temperature: 4500 Kelvin.
- > Temperature increase at head area: 0.5°C.
- > Total power consumption: 16 W.
- > Light source: 19 LED's.
- > Life span of over 60,000 hours.
- > Diameter of lamp head: 33 cm.
- Detachable sterilizable handle included.

Ceiling track system


- > Consisting of:
 - 250 cm aluminium track* and moveable carriage
 - 80 cm ceiling column*
 - 2 x two-part suspension arm
 - 40 x 50 cm shield
 - LED 130F lamp
- > Optional extras:
 - Second track carriage for two additional suspended devices.
 - Cable management system so lamp cables can be contained and managed within a separately supplied flexible energy chain.







Technical specification



Equipment weights & part numbers

350/45/LED130F-0031

Power supply in housing LED 130F lamp head: **2.4 kg** 40 cm x 50 cm lead glass shield: **12.5 kg** 2 x Suspension arm: **10.4 kg** (each) 80 cm dual mount ceiling column: **12.5 kg** 2.5 m ceiling track & carriage: **50 kg**

Optional equipment:

Dual mount ceiling column: 40 cm (#300/COLUMN/40): **10 kg**

60 cm (#300/COLUMN/60): **11.2 kg** 100 cm (#300/COLUMN/100): **14.7 kg**

Ceiling track & carriage: 4.2 m (#3001/TC/420): **72 kg**Track cable management: 2.5 m (#3001/TC/250/EC): **1.3 kg**4.2 m (#3001/TC/420/EC): **1.7 kg**

Additional track carriage: For use in 2.5 m or 4.2 m track (#3001/3.25): **4.6 kg**

