



Protective clothing

X-ray protective clothing

909 *LytaType* cross back apron

Features

- > Excellent design transfers weight from the shoulders to the hips.
- > Elasticated flaps fasten at the sides.

Tailor made

- > Tailor made *LytaType* personal x-ray protective clothing is available. Please contact us for required measurements.

LytaType colours and codes


Please note the colours shown are approximate. A colour swatch is available on request.



Royal
02



Navy
04



Poppy
11



Bottle Green
41



Model 909
Pocket 900/001 shown
as an optional extra



S Small for chest sizes (A) 80 – 90 cm girth

| Lead equivalent (Pb)* Front and back | Length (B) | Apron width shoulder / hip | Maximum girth of waist (C) or hip (D) | Product code |
|---|------------|-------------------------------|--|--------------|
| 0.25 / 0.25 mm | 85 cm | 40 cm / 60 cm | 100 cm | 909/22/085/S |
| " | 90 cm | " | " | 909/22/090/S |
| " | 100 cm | " | " | 909/22/100/S |
| " | 110 cm | " | " | 909/22/110/S |
| 0.35 / 0.25 mm | 85 cm | 40 cm / 60 cm | 100 cm | 909/32/085/S |
| " | 90 cm | " | " | 909/32/090/S |
| " | 100 cm | " | " | 909/32/100/S |
| " | 110 cm | " | " | 909/32/110/S |
| 0.50 / 0.25 mm | 85 cm | 40 cm / 60 cm | 100 cm | 909/52/085/S |
| " | 90 cm | " | " | 909/52/090/S |
| " | 100 cm | " | " | 909/52/100/S |
| " | 110 cm | " | " | 909/52/110/S |

*Pb: Lead vinyl in accordance with BS EN 61331-1:2014 in the 50 to 150 kV range of x-ray tube voltages.



Protective clothing

M Medium for chest sizes (A) 90 – 100 cm girth

| Lead equivalent (Pb)* Front and back | Length (B) | Apron width shoulder / hip | Maximum girth of waist (C) or hip (D) | Product code |
|---|------------|-------------------------------|--|--------------|
| 0.25 / 0.25 mm | 90 cm | 48 cm / 60 cm | 100 cm | 909/22/090/M |
| " | 100 cm | " | " | 909/22/100/M |
| " | 110 cm | " | " | 909/22/110/M |
| 0.35 / 0.25 mm | 90 cm | 48 cm / 60 cm | 100 cm | 909/32/090/M |
| " | 100 cm | " | " | 909/32/100/M |
| " | 110 cm | " | " | 909/32/110/M |
| 0.50 / 0.25 mm | 90 cm | 48 cm / 60 cm | 100 cm | 909/52/090/M |
| " | 100 cm | " | " | 909/52/100/M |
| " | 110 cm | " | " | 909/52/110/M |

*Pb: Lead vinyl in accordance with BS EN 61331-1:2014 in the 50 to 150 kV range of x-ray tube voltages.


L Large for chest sizes (A) 100 – 120 cm girth

| Lead equivalent (Pb)* Front and back | Length (B) | Apron width shoulder / hip | Maximum girth of waist (C) or hip (D) | Product code |
|---|------------|-------------------------------|--|--------------|
| 0.25 / 0.25 mm | 90 cm | 48 cm / 75 cm | 120 cm | 909/22/090/L |
| " | 100 cm | " | " | 909/22/100/L |
| " | 110 cm | " | " | 909/22/110/L |
| 0.35 / 0.25 mm | 90 cm | 48 cm / 75 cm | 120 cm | 909/32/090/L |
| " | 100 cm | " | " | 909/32/100/L |
| " | 110 cm | " | " | 909/32/110/L |
| 0.50 / 0.25 mm | 90 cm | 48 cm / 75 cm | 120 cm | 909/52/090/L |
| " | 100 cm | " | " | 909/52/100/L |
| " | 110 cm | " | " | 909/52/110/L |

*Pb: Lead vinyl in accordance with BS EN 61331-1:2014 in the 50 to 150 kV range of x-ray tube voltages.

Optional extras: -

| Description | Product code |
|--|--------------|
| Pocket | 900/001 |
| Embroidery in a position to be specified | 9/B20 |



Kenex are certified to Regulation (EU) 2016/425 (PPE) for the design and manufacture of x-ray protective clothing. LytaType aprons and thyroid collars comply with the requirements of BS EN 61331-3:2014 and BS EN 13402-3:2013. They include lead (Pb) vinyl material tested for use with a 50 to 150 kV range of x-ray tube voltages, as specified in BS EN 61331-1:2014.

Notified body: SGS Fimko Oy, P.O. Box 30 (Särkiniementie 3), 00211 Helsinki Finland.
Identification number CE 0598.